

Equipment for XL³ 4000

for modular devices, Vistop, DPX³ 160/250, DPX-IS 250 on rail

Equipment for XL³ 4000

for mounting on plate: DPX-IS 250, 630 and 1600



0 206 01



0 262 39



0 206 05




0 208 00



0 209 01



0 208 10



0 209 10

Pack	Cat.Nos	Fixing devices on rail
1	24 modules 36 modules 0 206 01 0 206 51	Rails Comprising: an aluminium profile rail and two 2-position fixing brackets Accept HX ³ 125 A plug-in connection row distribution blocks Fit onto functional uprights For mounting DPX ³ using fixing plates For fixing on XL ³ 800 and XL ³ 4000 functional uprights Accept wire guide Cat.No 4 052 25 (p. 275)
1	4 210 71	Fixing plates for mounting DPX³ on rail For mounting DPX ³ on aluminium rail or on plate Cat.Nos 0 206 11/61
1	4 210 73	For DPX ³ 160 without side motor-driven handle
1	4 210 68	For DPX ³ 160 with earth leakage module without side motor-driven handle
1	4 210 72	For all DPX ³ 160 devices with side motor-driven handle
1	4 210 74	For DPX ³ 250 without side motor-driven handle
1	4 210 69	For DPX ³ 250 with earth leakage module without side motor-driven handle
1	4 210 69	For all DPX ³ 250 devices with side motor-driven handle
1	0 262 39	Fixing plate for mounting DPX-IS 250 on rail For mounting devices on aluminium rail or on plate Cat.Nos 0 206 11/61 For DPX-IS 250
1	4 052 26	Rail height spacer Designed for simultaneous mounting of modular devices and DPX ³ 160/250 and DPX-IS 250 devices mounted on rail Cat.Nos 0 206 01/51 or plate Cat.Nos 0 206 11/61 For 20 modules

Pack	Cat.Nos	Metal faceplates	Diagram
1	24 modules 36 modules 0 208 00 ¹ 0 209 00 ²	For modular devices 1/4 turn With captive screws	
1	0 208 01 ¹ 0 209 01 ²	For Vistop up to 160 A 1/4 turn With captive screws	
1	0 208 10 ¹ 0 209 10 ²	For DPX³ and DPX-IS 250 1/4 turn With captive screws	

1: For fastening and sealing
2: Hinges Cat.No 0 209 59 available as an option

Pack	Cat.Nos	Plates for DPX-IS	Diagram
1	24 modules 36 modules 0 206 05 0 206 55	Direct fixing on functional uprights Fixed plates for device in vertical position For 1 or 2 DPX-IS 250 front or rear terminals	
1	0 206 07 0 206 57	For 1 DPX-IS 630 front or rear terminals	
1	0 211 00	For 1 DPX-IS 1600 or 1 DPX 1600 front terminals	
1	0 211 06 0 211 03	For 1 DPX-IS 1600 or 1 DPX 1600 rear terminals	
1	0 206 18	Fixed plates for device in horizontal position For 1 DPX-IS 250 front or rear terminals	
1	0 206 19	For 1 DPX-IS 630 front or rear terminals	
1	24 modules 36 modules 0 208 10 ¹ 0 209 10 ²	Metal faceplates For 1 DPX-IS 250 in vertical position 1/4 turn With captive screws ⁽²⁾	
1	0 208 06 ¹ 0 209 06 ²	For 2 DPX-IS 250 in vertical position 1/4 turn With captive screws	
1	0 209 18 ²	For 1 DPX-IS 250 in horizontal position With captive screws	
1	0 208 07 ¹ 0 209 07 ²	For 1 DPX-IS 630 in vertical position 1/4 turn With captive screws Does not allow the use of terminal shields Cat.No 0 262 45	
1	0 209 19 ²	For 1 DPX-IS 630 in horizontal position With captive screws	
1	24 modules 0 211 13 ²	For 1 DPX-IS 1600 in vertical position With captive screws	
1	0 208 36 ²	For 1 DPX-IS 1600 in horizontal position With captive screws	

1: For fastening and sealing
2: Hinges Cat.No 0 209 59 available as an option

Download XL³ 4000/6300
Workshop specifications on
www.docexport.legrand.com

