



MASTER PL-Electronic

MASTER PLE-R 20W/827 E27 220-240V 1CT/6

Non-covered energy-saving MASTER lamps - the perfect choice for end users who demand the best performance and reliability. With a wide product range with different wattages, it offers comprehensive choices to suit different usages and applications

Product data

General Information	
Cap-Base	E27 [E27]
Nominal Lifetime (Nom)	20000 h
Switching Cycle	50000X
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	1220 lm
Luminous Flux (Rated) (Nom)	1220 lm
Color Designation	Warm White (WW)
Lumen Maintenance 2000 h (Nom)	95 %
Luman Maintenanas E000 h (Nam)	
Lumen Maintenance 5000 h (Nom)	90 %
Chromaticity Coordinate X (Nom)	90 % 457
Chromaticity Coordinate X (Nom)	457
Chromaticity Coordinate X (Nom) Chromaticity Coordinate Y (Nom)	457 416
Chromaticity Coordinate X (Nom) Chromaticity Coordinate Y (Nom) Correlated Color Temperature (Nom)	457 416 2700 K
Chromaticity Coordinate X (Nom) Chromaticity Coordinate Y (Nom) Correlated Color Temperature (Nom) Luminous Efficacy (rated) (Nom)	457 416 2700 K 60 lm/W 82

Operating and Electrical	
Input Frequency	50 or 60 Hz
Power (Rated) (Nom)	20.0 W
Lamp Current (Nom)	140 mA
Starting Time (Nom)	1.0 s
Warm Up Time to 60% Light (Min)	10 s
Warm Up Time to 60% Light (Max)	60 s
Power Factor (Nom)	0.6
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Label (EEL)	A
Mercury (Hg) Content (Max)	1.5 mg
Mercury (Hg) Content (Nom)	1.41 mg
Energy Consumption kWh/1000 h	20 kWh

MASTER PL-Electronic

Product Data	
Floduct Data	
Full product code	871150075143010
Order product name	MASTER PLE-R 20W/827 E27 220-240V 1CT/6
EAN/UPC - Product	8711500751430
Order code	929746197004
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	6
Material Nr. (12NC)	929746197004
Net Weight (Piece)	91.000 g
ILCOS Code	FBT 20/27/1b-230/240-E27

Warnings and Safety

- Breaking a lamp is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a closed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Compact fluorescent lamps have to be treated as special waste, they must be taken to your local waste facilities for recycling. The European Lighting Industry has set up an infrastructure, capable of recycling mercury, other metals, glass etc.

Dimensional drawing





© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.